


USEQGSEAC82180

Aliases (USEQGSEAC82180)

KEMET, QGS, Gas Detection, SMD, Infrared, Small SMD Package, 12C Communication Compatible, High Dynamic Range



Click [here](#) for the 3D model.

Dimensions

L	5.65mm NOM
W	3.7mm NOM
T	1.55mm MAX

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	800
Typical Component Weight	70 mg

General Information

Series	QGS
Type	Gas Detection
Style	SMD
Description	12C
Features	Small SMD Package, 12C Communication Compatible, High Dynamic Range
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
SCIP Number	bc4e3452-d0d0-4c97-93bd-778b4e41f2f2
Qualifications	REACH
MSL	3

Specifications

Temperature Range	-40/+85°C
Power Supply Voltage	1.75 - 3.6 V
Current	1 - 23 uA (Supply Current, Typical)
D*	$2.5 \times 10^{-8} \text{ cm} \sqrt{\text{Hz}} / \text{W}$
NEP	$2.7 \times 10^{-10} \text{ W}/\sqrt{\text{Hz}}$
Time Constant	10ms (10-20 Hz peak)
Field of View	90 degrees
Element Size	0.64mm x 0.64mm
Filter	4.26um, BW: 180nm, Gas: CO2