


[Click here for the 3D model.](#)

General Information

Series	T598
Dielectric	Polymer Tantalum
Style	SMD Chip
Description	SMD, Polymer, Molded, Low ESR, AEC-Q200
Features	Automotive (Surge testing at -55C +/-5C and +85C +/-5C / 10 cycles)
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	434.8 mg
Shelf Life	52 Weeks
MSL	3

Dimensions

L	7.3mm +/-0.3mm	Capacitance	330 uF
W	4.3mm +/-0.3mm	Tolerance	20%
H	2.8mm +/-0.3mm	Voltage DC	6.3 VDC (105C), 4.22 VDC (125C)
T	0.13mm REF	Temperature Range	-55/+125C
S	1.3mm +/-0.3mm	Rated Temperature	105C
F	2.4mm +/-0.1mm	Humidity	85C, 85% RH, load, 1000 Hours
A	3.8mm MIN	Dissipation Factor	10% 120Hz 25C
B	0.5mm +/-0.15mm	Failure Rate	N/A
P	0.9mm REF	ESR	25 mOhms (100kHz 25C)
R	1mm REF	Ripple Current	4240 mA (rms, 100kHz 45C), 2968 mA (rms, 105C), 1060 mA (rms, 125C)
X	0.1mm +/-0.1mm REF	Leakage Current	207.9 uA (5min 25C)

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.