



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	1812
L	4.7mm +/-0.4mm
W	3.2mm +/-0.3mm
T	1.9mm MAX
B	0.5mm +/-0.25mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	1000

#### General Information

Supplier	KEMET
Series	VC
Type	Varistors
Style	SMD Chip
Description	Surface Mount Varistors
Features	Low Voltage
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, UL, AEC-Q200
AEC-Q200	Yes

#### Specifications

Voltage DC	125 VDC (25C)
Voltage AC	95 VAC
Temperature Range	-55/+125°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	150 VDC at 1mA
Clamping Voltage	250 V
Clamping Current	5 A (8/20 us MAX)
Surge Current	300 A (8/20 us MAX)
Energy	5.2 J (10/1000 us MAX)
Capacitance	340 pF (1kHz)