


[Click here for the 3D model.](#)

#### General Information

Supplier	KEMET
Series	VG
Type	Varistors
Style	SMD Chip
Description	Surface Mount Varistors
Features	ESD Supresion
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, AEC-Q200
AEC-Q200	Yes

#### Dimensions

L	1.6mm +/-0.2mm
W	0.8mm +/-0.1mm
T	0.95mm
B	0.5mm +/-0.25mm
Case Code (EIA / mm)	0603 / 1608

#### Specifications

Voltage DC	18 VDC (25C)
Voltage AC	14 VAC
Temperature Range	-55/+125°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	25 VDC at 1mA
Clamping Voltage	50 V
Clamping Current	2 A (8/20 us MAX)
Energy	0.05 J (10/1000 us MAX)
Power	0.003 W (MAX)
Capacitance	75 pF (1kHz)

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.