



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0201
L	0.6mm +/-0.03mm
W	0.3mm +/-0.03mm
T	0.3mm +/-0.03mm
B	0.15mm +/-0.05mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	15000

#### General Information

Series	Z-SMS
Style	SMD Chip
Description	Chip Bead Signal Line
Features	Suppresses The XL Component; Helps Stop The Reduction Of The Wave-Form Integrity
RoHS	Yes
Notes	Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BBSY00060303241Y00">https://productfinder.pulseelectronics.com/part/BBSY00060303241Y00</a> .

#### Specifications

Impedance	240 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	200 mA (MAX)
Temperature Range	-55/+125°C
DC Resistance	0.8 Ohms