



### General Information

Series	QGSM
Type	Gas Detection
Style	SMD
Description	12C Gas Sensor Module
Features	Small SMD Package, 12C Communication Compatible, High Dynamic Range
RoHS	With Exemptions
REACH	SVHC (PZT - CAS 12626-81-2)
Qualifications	REACH
MSL	3

### Specifications

Temperature Range	-40/+85°C
Power Supply Voltage	1.75 - 3.6 V
Current	1 - 23 uA (Supply Current, Typical)
Miscellaneous	Includes sensor: USEQGSEH950180.
D*	$2.5 \times 10^8 \text{ cm} \sqrt{\text{Hz}} / \text{W}$
NEP	$2.7 \times 10^{-10} \text{ W}/\sqrt{\text{Hz}}$
Time Constant	10ms (10-20 Hz peak)
Field of View	90 degrees
Element Size	0.64mm x 0.64mm
Filter	9.5um, BW: 400nm, Sugar, Ethanol

### Dimensions

L	13.8mm NOM
W	16mm NOM
L2	10mm

### Packaging Specifications

Packaging Quantity	1
Typical Component Weight	5.41 g