



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0603
L	1.6mm +/-0.2mm
W	0.8mm +/-0.1mm
T	0.95mm MAX
B	0.5mm +/-0.25mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	3500

#### General Information

Supplier	KEMET
Series	VC
Type	Varistors
Style	SMD Chip
Description	Surface Mount Varistors
Features	Low Voltage
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, UL, AEC-Q200
AEC-Q200	Yes

#### Specifications

Voltage DC	22 VDC (25C)
Voltage AC	17 VAC
Temperature Range	-55/+125°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	27 VDC at 1 mA
Clamping Voltage	44 V
Clamping Current	1 A (8/20 us MAX)
Surge Current	30 A (8/20 us MAX)
Energy	0.3 J (10/1000 us MAX)
Capacitance	185 pF (1kHz)