



Click [here](#) for the 3D model.

Dimensions

Chip Size	2220
L	5.7mm +/-0.5mm
W	5mm +/-0.4mm
T	1.9mm MAX
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	1000

General Information

Series	VC
Type	Varistors
Style	SMD Chip
Description	Surface Mount Varistors
Features	Low Voltage
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, UL, AEC-Q200
AEC-Q200	Yes

Specifications

Voltage DC	170 VDC (25C)
Voltage AC	130 VAC
Temperature Range	-55/+125°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	205 VDC at 1 mA
Clamping Voltage	340 V
Clamping Current	10 A (8/20 us MAX)
Surge Current	500 A (8/20 us MAX)
Energy	7.4 J (10/1000 us MAX)
Capacitance	500 pF (1kHz)