



Click [here](#) for the 3D model.

Dimensions

Chip Size	1206
L	3.2mm +/-0.3mm
W	1.6mm +/-0.2mm
T	0.85mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

General Information

Supplier	KEMET
Series	VE
Type	Varistors
Style	SMD Chip
Description	Surface Mount Varistors
Features	Low Voltage High Temperature
Termination	Nickel Tin
RoHS	With Exemptions
Qualifications	IEC, UL, AEC-Q200
AEC-Q200	Yes

Specifications

Voltage DC	18 VDC (25C)
Voltage AC	14 VAC
Temperature Range	-55/+150°C
Storage Temperature Range	-55/+150°C
Varistor Voltage	22 VDC at 1 mA
Clamping Voltage	40 V
Clamping Current	1 A (8/20 us MAX)
Surge Current	200 A (8/20 us MAX)
Energy	0.6 J (10/1000 us MAX)
Capacitance	950 pF (1kHz)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.