



Click [here](#) for the 3D model.

Dimensions

L	7.62mm MAX
W	7.62mm MAX
T	3.81mm MAX
S	5.08mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1

General Information

Series	VRR Indust X7R HVHT200C
Style	Radial
Description	Commercial, High Temperature, High Voltage
Features	High Temperature, High Voltage, Commercial
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	d1f8aba3-2564-4904-a1cf-714fe85ef1ab
Termination	Gold
Failure Rate	N/A
Testing and Reliability	MIL-PRF-20 Group A
Qualifications	MIL-PRF-20 Group A
AEC-Q200	No

Specifications

Capacitance	470 pF
Capacitance Tolerance	10%
Voltage DC	500 VDC
Dielectric Withstanding Voltage	750 VDC
Temperature Range	-55/+200°C
Temperature Coefficient	X7R
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Insulation Resistance	100 GOhms