

## A50QT3220AA00K

Aliases (50QT3220AA00K)

A50, Film, Metallized Polyester, Automotive Grade, 0.22 uF, 10%, 1,000 VDC, 250 VAC, 85°C

**FRONT VIEW**



**SIDE VIEW**



Click [here](#) for the 3D model.

### General Information

Series	A50
Dielectric	Metallized Polyester
Style	Axial
Features	Automotive Grade
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	9 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C. maxKO = 20000.

### Dimensions

D	16mm MAX
L	33mm MAX
LL	40mm +/-5mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	200

### Specifications

Capacitance	0.22 uF
Tolerance	10%
Voltage DC	1000 VDC, 750 VDC (105C)
Voltage AC	250 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	10 V/us
Inductance	7 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.