



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0603
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.15mm
B	0.3mm +/-0.2mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	4000

#### General Information

Series	Z-PMS
Style	SMD Chip
Description	Chip Bead, Power Line
Features	Suppresses The XL Component; Helps Stop The Reduction Of The Wave-Form Integrity
RoHS	Yes
Notes	Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BBPY00160808101Y00">https://productfinder.pulseelectronics.com/part/BBPY00160808101Y00</a> .

#### Specifications

Impedance	100 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	1700 mA (MAX)
Temperature Range	-55/+85°C
DC Resistance	0.05 Ohms