



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0805
L	2mm -3mm
W	1.25mm +/-0.2mm
T	0.85mm +/-0.2mm
B	0.5mm +/-0.3mm

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

#### General Information

Series	Z-SMS
Style	SMD Chip
Description	Chip Bead Signal Line
Features	Intended For Noise Suppression Around 200MHz, Effectively Increase Attenuation
RoHS	Yes
Notes	Suggested Replacement - <a href="https://www.chilisin.com/en-global/Inductor/Product/BBBK_201209/BBBK00201209252Y00">https://www.chilisin.com/en-global/Inductor/Product/BBBK_201209/BBBK00201209252Y00</a> .

#### Specifications

Impedance	2500 Ohms (100 MHz)
Impedance Tolerance	25%
Ripple Current	200 mA (MAX)
Temperature Range	-55/+125°C
DC Resistance	0.75 Ohms