


## A72QT3100AA02M

Aliases (72QT3100AA02M)

## Obsolete

A72, Film, Film/Foil Polypropylene, General Purpose, 0.1 uF, 20%, 1,000 VDC, 400 VAC, 85°C



## **General Information** A72 Series Dielectric Film/Foil Polypropylene Style Axial RoHS Yes Wire Leads Lead AEC-Q200 No Typical Component Weight 11.5 g Above 85C DC And AC Voltage Derating Is 1.25%/C. maxK0 = 7400000. Miscellaneous

## **SIDE VIEW**



Click here for the 3D model.

Dimensions	
D	19mm MAX
L	33mm MAX
LL	40mm +/-5mm
F	1mm +/-0.05mm
Packaging Specifications	

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	150

Specifications	
Capacitance	0.1 uF
Tolerance	20%
Voltage DC	1000 VDC, 750 VDC (105C)
Voltage AC	400 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 10kHz, 0.1% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	3,700 V/us
Inductance	33 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/31/2025 © 2006 - 2025 YAGEO