


KPS-MCC Indust COG HT200C, Ceramic, 200C, 0.2 uF, 10%, 2000 VDC, COG



Dimensions	
D	25.64mm +/-0.635mm
L	6.35mm MIN
H	2.54mm NOM
F	1.397mm +/-0.25mm
A	13.46mm MAX
B	15.238mm MAX
C	11.43mm +/-0.635mm
E	12.7mm MAX
K	0.5mm NOM

Packaging Specifications	
Packaging Quantity:	16

General Information	
Supplier:	KEMET
Series:	KPS-MCC Indust COG HT200C
Style:	Leaded Stacked Chip
Description:	Low ESR, Stacked Ceramic Chips
Features:	200C, Low ESR, High Thermal Stability, Bulk Capacitance
RoHS:	With Exemptions
Termination:	Silver
Lead:	Straight Leads
Notes:	Note: Number Of Chips In Stack Depends On Design. Number Of Chips In This Stack = 10

Specifications	
Capacitance:	0.2 uF
Capacitance Tolerance:	10%
Voltage DC:	2000 VDC
Dielectric Withstanding Voltage:	2,400 V
Temperature Range:	-55/+200C
Temperature Coefficient:	COG
Dissipation Factor:	0.10% 1kHz 25C
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	5 GOhms