


75HV33B152KC

HV RAD-LDD Indust X7R HV, Ceramic, 1,500 pF, 10%, 7,500 VDC, X7R, Radial Leaded Multilayer Ceramic Capacitor, 17.78 mm



Click [here](#) for the 3D model.

General Information

Series	HV RAD-LDD Indust X7R HV
Style	Radial
Description	Radial Leaded Multilayer Ceramic Capacitor
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	ef26097b-3862-4ee0-b0ad-404a563ece0f
Termination	Copper
Lead	Wire Leads
AEC-Q200	No

Specifications

Capacitance	1,500 pF
Tolerance	10%
Voltage DC	7500 VDC
Dielectric Withstanding Voltage	9,000 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Aging Rate	2% Loss/Decade Hour
Insulation Resistance	100 GOhms

Dimensions

L	21.59mm MAX
H	10.16mm MAX
T	6.89mm MAX
S	17.78mm +/-0.762mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications

Packaging	Waffle, Tray
Packaging Quantity	20

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.