


## ALC70A161BB350

ALC70, Aluminum, Aluminum Electrolytic, 160 uF, 20%, 350 VDC, -40/+85°C, 10 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                     |
|--------------------------|-------------------------------------|
| Series                   | ALC70                               |
| Dielectric               | Aluminum Electrolytic               |
| Description              | Snap-In, Aluminum Electrolytic      |
| RoHS                     | Yes                                 |
| Lead                     | 2 Pin                               |
| AEC-Q200                 | No                                  |
| Halogen Free             | Yes                                 |
| Typical Component Weight | 28 g                                |
| Notes                    | Dimensions D And L Include Slewing. |
| Shelf Life               | 156 Weeks                           |

### Specifications

|                   |   |
|-------------------|---|
| Capacitance       | 160 uF  |
| Tolerance         | 20%   |
| Voltage DC        | 350 VDC, 385 VDC (Surge)  |
| Temperature Range | -40/+85°C   |
| Rated Temperature | 85°C  |
| Life              | 10000 Hrs (Rated Voltage And Ripple Current At 85°C), 16000 Hrs (Rated Voltage at 85°C) |
| ESR               | 873.4 mOhms (100Hz 20°C), 453.9 mOhms (10kHz 20°C)                                      |
| Ripple Current    | 1.023 Amps (100Hz 85°C), 2.524 Amps (10kHz 85°C)  |
| Leakage Current   | 336 uA (5min 20°C)  |

### Dimensions

|    |               |
|----|---------------|
| D  | 25mm +1mm     |
| L  | 30mm +/-2mm   |
| S  | 10mm +/-0.1mm |
| LL | 6.3mm +/-1mm  |
| F  | 2mm +/-0.1mm  |

### Packaging Specifications

|           |           |
|-----------|-----------|
| Slewing   | Yes       |
| Packaging | Bulk, Bag |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.