



Click [here](#) for the 3D model.

Dimensions	
W	25.1mm +/-0.1mm
W2	25.5mm MAX
H	20mm +/-0.1mm
T	25.1mm +/-0.1mm
T2	25.5mm MAX
LL	100mm +/-5mm

Packaging Specifications	
Typical Component Weight	105
Packaging	Bulk
Packaging Quantity	1

General Information	
Style	Resin Coated
Description	Resin Coated Type Multilayer Piezoelectric Actuators
Young's Modulus	4.4x10 ¹⁰ N/m ²
RoHS	With Exemptions
SCIP Number	294b4799-b00c-43e2-a15f-798c927a3ac8
REACH	SVHC (PZT - CAS 12626-81-2)

Specifications	
Series	AE
Displacement	15.6um +/-2um
Voltage DC	150 VDC
Capacitance	30.5 uF
Capacitance Tolerance	20%
Resonant Frequency	69 kHz
Tensile Strength	2000 N
Generated Force	20000 N
Stiffness	1282 N/um
Insulation Resistance	0.4 MOhms
Temperature Range	-25/+85°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.