

ALC40A122EP400

ALC40, Aluminum, Aluminum Electrolytic, 1,200 uF, 20%, 400 VDC, -40/+105°C, 10 mm



Click [here](#) for the 3D model.

Dimensions	
D	40mm +1mm
L	105mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Packaging	Tray

General Information	
Series	ALC40
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No
Typical Component Weight	170 g
Shelf Life	156 Weeks

Specifications	
Capacitance	1,200 uF
Tolerance	20%
Voltage DC	400 VDC, 440 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	9000 Hrs (Rated Voltage And Ripple Current At 105C), 14000 Hrs (Rated Voltage at 105C)
ESR	103 mOhms (100Hz 20C), 70 mOhms (10kHz 20C)
Ripple Current	5.76 Amps (100Hz 105C), 11.46 Amps (10kHz 105C)
Leakage Current	1440 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.