

## ALF70C561EL630

ALF70, Aluminum, Aluminum Electrolytic, 560 uF, 20%, 630 VDC, -40/+85°C, 22.5 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                     |
|--------------------------|-------------------------------------|
| Series                   | ALF70                               |
| Dielectric               | Aluminum Electrolytic               |
| Style                    | Press-Fit                           |
| Description              | Aluminum Electrolytic               |
| RoHS                     | Yes                                 |
| Lead                     | 4 Pin Press-Fit                     |
| AEC-Q200                 | No                                  |
| Halogen Free             | Yes                                 |
| Typical Component Weight | 165 g                               |
| Notes                    | Dimensions D And L Include Slewing. |
| Shelf Life               | 156 Weeks                           |

### Specifications

|                   |                                                                                         |
|-------------------|-----------------------------------------------------------------------------------------|
| Capacitance       | 560 uF                                                                                  |
| Tolerance         | 20%                                                                                     |
| Voltage DC        | 630 VDC, 690 VDC (Surge)                                                                |
| Temperature Range | -40/+85°C                                                                               |
| Rated Temperature | 85°C                                                                                    |
| Life              | 18000 Hrs (Rated Voltage And Ripple Current At 85°C), 29000 Hrs (Rated Voltage At 85°C) |
| ESR               | 240.7 mOhms (100Hz 20C), 166 mOhms (10kHz 20C)                                          |
| Ripple Current    | 3.945 Amps (100Hz 85C), 8.015 Amps (10kHz 85C)                                          |
| Leakage Current   | 2117 uA (5min 20°C)                                                                     |

### Dimensions

|    |                    |
|----|--------------------|
| D  | 40mm +1mm          |
| L  | 80mm +/-2mm        |
| S  | 22.5mm +/-0.1mm    |
| LL | 5.5mm +/-1mm       |
| F  | 1.486mm +/-0.076mm |

### Packaging Specifications

|           |      |
|-----------|------|
| Slewing   | Yes  |
| Packaging | Bulk |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.