



Click [here](#) for the 3D model.

General Information

Series	ALN20S
Dielectric	Aluminum Electrolytic
Description	Audio Specific Aluminum Electrolytic
Features	Audio Grade
RoHS	Yes
Lead	4 Pin Solder Tags
AEC-Q200	No
Typical Component Weight	170 g
Notes	Dimensions D And L Include Slewing.

Specifications

Capacitance	10,000 uF
Tolerance	20%
Voltage DC	100 VDC, 115 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	18000 Hrs
Leakage Current	6000 uA (5min 20°C)

Dimensions

D	40mm +/-1mm
L	105mm +/-2mm
S	25mm
LL	6.3mm +/-1mm
F	1.3mm

Packaging Specifications

Slewing	Yes
Packaging	Tray