


## ALS30A681DB250

ALS30, Aluminum, Aluminum Electrolytic, 680 uF, 20%, 250 VDC, -40/+85°C, 12.8 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                                                                                     |
|--------------------------|-----------------------------------------------------------------------------------------------------|
| Series                   | ALS30                                                                                               |
| Dielectric               | Aluminum Electrolytic                                                                               |
| Description              | Screw Terminal, Aluminum Electrolytic                                                               |
| RoHS                     | Yes                                                                                                 |
| Lead                     | Screw Terminals M5                                                                                  |
| Mounting                 | Through-Hole                                                                                        |
| AEC-Q200                 | No                                                                                                  |
| Typical Component Weight | 90 g                                                                                                |
| Notes                    | Dimensions D And L Include Sleeving. MS (MxH) = M8x12. Mounting Clamp (Sold Separately): V3/H2/2736 |
| Shelf Life               | 156 Weeks                                                                                           |

### Specifications

|                   |                                                                                         |
|-------------------|-----------------------------------------------------------------------------------------|
| Capacitance       | 680 uF                                                                                  |
| Tolerance         | 20%                                                                                     |
| Voltage DC        | 250 VDC, 288 VDC (Surge)                                                                |
| Temperature Range | -40/+85°C                                                                               |
| Rated Temperature | 85°C                                                                                    |
| Life              | 11000 Hrs (Rated Voltage And Ripple Current At 85°C), 22000 Hrs (Rated Voltage At 85°C) |
| ESR               | 172 mOhms (100Hz 20°C), 131 mOhms (10kHz 20°C)                                          |
| Ripple Current    | 3.8 Amps (100Hz 85°C), 5.6 Amps (10kHz 85°C)                                            |
| Leakage Current   | 1020 uA (5min 20°C)                                                                     |

### Dimensions

|    |                 |
|----|-----------------|
| D  | 36mm +/-1mm     |
| L  | 62mm +/-2mm     |
| T  | 7.1mm +/-0.5mm  |
| S  | 12.8mm +/-0.5mm |
| DT | 8mm +/-0.5mm    |
| LT | 67.5mm +/-1mm   |
| TD | 10mm MIN        |
| V  | 8mm NOM         |

### Packaging Specifications

|           |           |
|-----------|-----------|
| Sleeving  | Yes       |
| Packaging | Bulk, Box |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.