

C0402C474K9PACTU

Aliases (C0402C474K9PAC7867) SMD Comm X5R, Ceramic, 0.47 uF, 10%, 6.3 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 0402, 0.3 mm



General Information		
Series	SMD Comm X5R	
Style	SMD Chip	
Description	SMD, MLCC, Temperature Stable, Class II	
Features	Temperature Stable, Class II	
RoHS	Yes	
Termination	Tin	
Marking	No	
AEC-Q200	No	
Typical Component Weight	1.21 mg	
Shelf Life	78 Weeks	
MSL	1	

0.47 uF

Dimensions	
Chip Size	0402
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
Т	0.5mm +/-0.05mm
S	0.3mm MIN
В	0.3mm +/-0.1mm

	1mm +/-0.05mm	Measurement Condition	1 kHz 1.0Vrms
	0.5mm +/-0.05mm	Tolerance	10%
	0.5mm +/-0.05mm	Voltage DC	6.3 VDC
	0.3mm MIN	Dielectric Withstanding Voltage	15.75 VDC
	0.3mm +/-0.1mm	Temperature Range	-55/+85°C
		Temp. Coefficient	X5R
tions	T&R, 180mm, Paper Tape	Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 0.5Vrms
	10000	Dissipation Factor	10% 1 kHz 1.0Vrms
		Aging Rate	5% Loss/Decade Hour: Referee

Specifications

Capacitance

W	0.5mm +/-0.05mm	Tolerance	10%
Т	0.5mm +/-0.05mm	Voltage DC	6.3 VDC
S	0.3mm MIN	Dielectric Withstanding Voltage	15.75 VDC
В	0.3mm +/-0.1mm	Temperature Range	-55/+85°C
		Temp. Coefficient	X5R
Packaging Specifications		Capacitance Change with	15%, 1kHz 0.5Vrms
Packaging	T&R, 180mm, Paper Tape	Reference to +25°C and 0 VDC Applied (TCC)	
Packaging Quantity 10000	Dissipation Factor	10% 1 kHz 1.0Vrms	
		Aging Rate	5% Loss/Decade Hour: Referee Time is 48 Hours
		Insulation Resistance	1.0638 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO




C0402C474K9PACTU

Aliases (C0402C474K9PAC7867) SMD Comm X5R, Ceramic, 0.47 uF, 10%, 6.3 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 0402, 0.3 mm

Simulations

For the complete simulation environment please visit Y-SIM.



Generated 10/16/2025 © 2006 - 2025 YAGEO

0.0

3.0

Voltage (VDC)

5.0

-80.0

10.0 k 100.0 k 1.0 M 10.0 M 100.0 M 1.0 G

Frequency (Hz)



C0402C474K9PACTU

Aliases (C0402C474K9PAC7867) SMD Comm X5R, Ceramic, 0.47 uF, 10%, 6.3 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 0402, 0.3 mm

These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR in the "Temperature Rise vs. Ripple Current" plots is the ESR at ambient temperature. The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated. The effects shown herein are based on measured data from a multiple part sample of the parts in question. Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

 The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

 Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 10/16/2025 © 2006 - 2025 YAGEO