

## C0603T472J5RCCTU

Aliases (C0603T472J5RCC7867)

SMD COTS X7R, Ceramic, 4,700 pF, 5%, 50 VDC, X7R, SMD, MLCC, COTS, Temperature Stable, Class II, 0603, 0.5 mm



Click [here](#) for the 3D model.

### General Information

|                          |                                                                                                      |
|--------------------------|------------------------------------------------------------------------------------------------------|
| Series                   | SMD COTS X7R                                                                                         |
| Style                    | SMD Chip                                                                                             |
| Description              | SMD, MLCC, COTS, Temperature Stable, Class II                                                        |
| Features                 | Temperature Stable, Class II                                                                         |
| RoHS                     | Yes                                                                                                  |
| Termination              | Tin                                                                                                  |
| Marking                  | No                                                                                                   |
| Failure Rate             | Testing per MIL-PRF-55681 PDA 8%, DPA per EIA-469, Humidity per MIL-STD-202, Method 103, Condition A |
| AEC-Q200                 | No                                                                                                   |
| Typical Component Weight | 4.8 mg                                                                                               |
| Shelf Life               | 78 Weeks                                                                                             |
| MSL                      | 1                                                                                                    |

### Dimensions

|           |                  |
|-----------|------------------|
| Chip Size | 0603             |
| L         | 1.6mm +/-0.15mm  |
| W         | 0.8mm +/-0.15mm  |
| T         | 0.8mm +/-0.07mm  |
| S         | 0.5mm MIN        |
| B         | 0.35mm +/-0.15mm |

### Packaging Specifications

|                    |                        |
|--------------------|------------------------|
| Packaging          | T&R, 180mm, Paper Tape |
| Packaging Quantity | 4000                   |

### Specifications

|                                                                    |                                                 |
|--------------------------------------------------------------------|-------------------------------------------------|
| Capacitance                                                        | 4,700 pF                                        |
| Measurement Condition                                              | 1 kHz 1.0Vrms                                   |
| Tolerance                                                          | 5%                                              |
| Voltage DC                                                         | 50 VDC                                          |
| Dielectric Withstanding Voltage                                    | 125 VDC                                         |
| Temperature Range                                                  | -55/+125°C                                      |
| Temp. Coefficient                                                  | X7R                                             |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor                                                 | 2.5% 1 kHz 1.0Vrms                              |
| Aging Rate                                                         | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance                                              | 100 GOhms                                       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.