


## C1206C511MFGACAUTO7210

SMD Auto COG HV, Ceramic, 510 pF, 20%, 1,500 VDC, COG, SMD, MLCC, Ultra-Stable, Low Loss, High Voltage, Automotive Grade, 1206, 1.5 mm



| General Information      |   |
|--------------------------|---|
| Series                   | SMD Auto COG HV   |
| Style                    | SMD Chip  |
| Description              | SMD, MLCC, Ultra-Stable, Low<br>Loss, High Voltage, Automotive<br>Grade |
| Features                 | Ultra-Stable, Low Loss,<br>Automotive Grade                             |
| RoHS                     | Yes   |
| Termination              | Tin   |
| Marking                  | No  |
| Qualifications           | AEC-Q200  |
| AEC-Q200                 | Yes   |
| Typical Component Weight | 36 mg   |
| Shelf Life               | 78 Weeks  |
| MSL                      | 1   |

| 5            |
|--------------|
| nm +/-0.2mm  |
| nm +/-0.2mm  |
| nm +/-0.15mm |
| nm MIN       |
| nm +/-0.25mm |
| ו            |

| Packaging Specifications |                          |
|--------------------------|--------------------------|
| Packaging                | T&R, 330mm, Plastic Tape |
| Packaging Quantity       | 8000                     |

| Specifications   |                           |
|--|---------------------------|
| Capacitance  | 510 pF                    |
| Measurement Condition  | 1 MHz 1.0Vrms             |
| Tolerance  | 20%                       |
| Voltage DC   | 1500 VDC                  |
| Dielectric Withstanding Voltage  | 1,800 VDC                 |
| Temperature Range  | -55/+125°C                |
| Temp. Coefficient  | COG                       |
| Capacitance Change with<br>Reference to +25°C and 0 VDC<br>Applied (TCC) | 30 ppm/C, 1MegaHz 1.0Vrms |
| Dissipation Factor   | 0.1% 1 MHz 1.0Vrms        |
| Aging Rate   | 0% Loss/Decade Hour       |
| Insulation Resistance  | 100 GOhms                 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO