


**General Information** 

Series RoHS



Aliases (C124K103K1X5CA) LDD Mil X7R C11015, Ceramic, 0.01 uF, 10%, 100 VDC, BX



Click

I ★		
F D	Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
	SCIP Number	f30e2214-6f19-489b-928a-4aa9 281a81a7
	Termination	Lead (SnPb)
	Lead	Wire Leads
	Failure Rate	N/A
	Testing and Reliability	MIL-PRF-11015
	Qualifications	MIL-PRF-11015
chere for the 3D model.	AEC-Q200	No
	C: f:+:	

Dimensions	
D	2.29mm +/-0.25mm
L	6.35mm +/-0.25mm
LL	31.75mm MIN
F	0.41mm +0.15/-0.03mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	200

Specifications	
Capacitance	0.01 uF
Tolerance	10%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	BX
Dissipation Factor	2.5%

LDD Mil X7R C11015

No

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/19/2025 © 2006 - 2025 YAGEO