
C2220C225M4R2L7186







Click here for the 3D model.

| General Information | |
|--------------------------|--------------------------------------------------------------------------|
| Series | KPS SMD Comm X7R SnPb |
| Style | Stacked Chip |
| Description | SMD, MLCC, Stacked, Double Chip, Temperature Stable |
| Features | Temperature Stable |
| RoHS | No |
| Prop 65 | WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov / |
| SCIP Number | 795b247e-78a9-405c-8728-22 3c2d9782a2 |
| Termination | Lead (SnPb) |
| AEC-Q200 | No |
| Typical Component Weight | 800 mg |
| Chip Size | 2220-2 |
| Shelf Life | 78 Weeks |
| MSL | 1 |

| Dimensions | |
|--------------------------|----------------|
| L | 6mm +/-0.5mm |
| W | 5mm +/-0.5mm |
| Т | 5mm +/-0.50mm |
| В | 1.6mm +/-0.3mm |
| | |
| Packaging Specifications | |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 200 |

| Specifications | |
|--------------------------------------------------------------------------|----------------------------------------------------|
| Capacitance | 2.2 uF |
| Measurement Condition | 1 kHz 1.0Vrms |
| Tolerance | 20% |
| Voltage DC | 16 VDC |
| Dielectric Withstanding Voltage | 40 VDC |
| Temperature Range | -55/+125°C |
| Temp. Coefficient | X7R |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms |
| Dissipation Factor | 3.5% 1 kHz 1.0Vrms |
| Aging Rate | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance | 454.5 MOhms |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/26/2025 © 2006 - 2025 YAGEO