


## C192C562J1G5CA7200









Click here for the 3D model.

General Information	
Series	LDD Comm COG
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	f30e2214-6f19-489b-928a-4aa 9281a81a7
Termination	Lead (SnPb)
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No
Notes	Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk.

Dimensions		
D	3.56mm +/-0.254mm	
L	9.91mm +/-0.254mm	
LL	38.1mm MIN	
F	0.64mm +0.1/-0.025mm	
Packaging Specifications		
Packaging	T&R	

D	3.56mm +/-0.254mm	Capacitance	5,600 pF
L	9.91mm +/-0.254mm	Tolerance	5%
LL	38.1mm MIN	Voltage DC	100 VDC
F	0.64mm +0.1/-0.025mm	Dielectric Withstanding Voltage	250 VDC
		Temperature Range	-55/+125°C
Packaging Specifications		Temp. Coefficient	COG
Packaging	T&R	Dissipation Factor	0.1% 1 kHz 25C
Packaging Quantity	3000	Insulation Resistance	179 MOhms

**Specifications** 

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/21/2025 © 2006 - 2025 YAGEO