


C2220H123JDGACTU

Aliases (C2220H123JDGAC7800)

Specifications

Insulation Resistance

SMD Indust COG HVHT200C, Ceramic, 0.012 uF, 5%, 1,000 VDC, COG, SMD, MLCC, High Temperature, Ultra-Stable, Low Loss, 3.5 mm, 2220 / 5651



General Information	
Series	SMD Indust COG HVHT200C
Style	SMD Chip
Description	SMD, MLCC, High Temperature, Ultra-Stable, Low Loss
Features	High Temp, Ultra-Stable, Low Loss
RoHS	Yes
Termination	Tin
Marking	No
AEC-Q200	No
Typical Component Weight	320 mg
Shelf Life	78 Weeks
MSL	1

Dimensions	
L	5.7mm +/-0.4mm
W	5mm +/-0.4mm
Т	2.5mm +/-0.20mm
S	3.5mm MIN
В	0.6mm +/-0.35mm
Case Code (EIA / mm)	2220 / 5651

Capacitance	0.012 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	5%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	1,200 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1kHz 1.0Vrms
Dissipation Factor	0.1% 1 kHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour

83.3333 GOhms

Packaging Specifications	
Packaging	T&R, 180mm, Plastic Tape
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and	
we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the	
requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us	
with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.	

Generated 12/03/2025 © 2006 - 2025 YAGEO