

General Information

Series

Style

Description




GoldMax 300 Comm X7R, Ceramic, 0.022 uF, 20%, 50 VDC, X7R, GoldMax, Commercial Standard, 5.08 mm

GoldMax 300 Comm X7R

GoldMax, Commercial Standard

Radial



2.01 MAV	Cit	0.022E
Dimensions	Specifications	
	Halogen Free	Yes
Seating Plane Seating Plane Click here for the 3D model.	AEC-Q200	No
	Failure Rate	N/A
	Lead	Wire Leads
	Termination	Lead (SnPb)
	SCIP Number	d4c83dcf-Oaf3-4f6a-8c42-c84 Ocabd6f5b
	Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
	RoHS	No

Dimensions	
L	3.81mm MAX
Н	5.08mm MAX
Т	2.54mm MAX
S	5.08mm +/-0.78mm
LL	7mm MIN
F	0.51mm +0.1/-0.025mm

Packaging Specifications		
Packaging	Bulk, Bag	
Packaging Quantity	500	

Specifications	
Capacitance	0.022 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	20%
Voltage DC	50 VDC
Dielectric Withstanding Voltage	125 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	0.15, 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Aging Rate	3% Loss/Decade Hour
Insulation Resistance	45.45 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/25/2025 © 2006 - 2025 YAGEO