


C330C104KDR5TA7303

Aliases (C330C104KDR5TATR)
GoldMax 300 Comm X7R HV, Ceramic, 0.1 uF, 10%, 1,000 VDC, X7R, GoldMax, Commercial Standard, 5.08 mm



General Information	
Series	GoldMax 300 Comm X7R HV
Style	Radial
Description	GoldMax, Commercial Standard
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A
AEC-Q200	No
Halogen Free	Yes

Click here for the 3D model.

Dimensions	
L	7.62mm MAX
Н	9.14mm MAX
Т	5.08mm MAX
S	5.08mm +/-0.78mm
НО	18mm MIN
F	0.51mm +0.1/-0.025mm

Packaging Specifications		
Packaging	T&R, 305mm	
Packaging Quantity	1500	

Specifications	
Capacitance	0.1 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	10%
Voltage DC	1000 VDC
Dielectric Withstanding Voltage	1,200 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	0.15, 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0 Vrms
Aging Rate	3% Loss/Decade Hour: Referee Time is 1000 Hours
Insulation Resistance	1GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO