

General Information

Series

Style

Description




GoldMax 300 Comm Z5U, Ceramic, 0.33 uF, 20%, 100 VDC, Z5U, GoldMax, Commercial Standard, 5.08 mm

GoldMax 300 Comm Z5U

GoldMax, Commercial Standard

Radial



Seating Plane Seating Plane Click here for the 3D model.	RoHS	No
	Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
	SCIP Number	d4c83dcf-0af3-4f6a-8c42-c84 Ocabd6f5b
	Termination	Lead (SnPb)
	Lead	Wire Leads
	Failure Rate	N/A
	AEC-Q200	No
	Halogen Free	Yes
Dimensions	Specifications	

Dimensions	
L	7.11mm MAX
Н	10.16mm MAX
Т	4.07mm MAX
S	5.08mm +/-0.78mm
LL	7mm MIN
F	0.51mm +0.1/-0.025mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	250

Specifications	
Capacitance	0.33 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	20%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	+10/+85°C
Temp. Coefficient	Z5U
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	'+22%/-56%, 1kHz 1.0Vrms
Dissipation Factor	4% 1 kHz 1.0Vrms
Aging Rate	7% Loss/Decade Hour
Insulation Resistance	300 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/17/2025 © 2006 - 2025 YAGEO