



Dimensions

| Packaging Specifications | |
|--------------------------|---------------|
| Mounting | Bolt - M12x16 |
| Packaging | Bulk, Bag |

| Specifications | |
|-----------------------|---------------------|
| Capacitance | 250 uF |
| Capacitance Tolerance | 5% |
| Voltage AC | 440 VAC |
| Voltage DC | 1000 VDC |
| Temperature Range | -25/+70°C |
| Rated Temperature | 70°C |
| Max dV/dt | 20 V/us |
| ESR | 1.7 mOhms (10kHz) |
| Ripple Current | 60 Amps (10kHz 40C) |
| Inductance | 175 nH |

Generated 4/24/2024 - 6c55319a-e27a-4510-8f94-eae26d234a6a