



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | C44U-M |
| Dielectric | Metallized Polypropylene |
| Style | Can |
| Features | DC Filtering, Energy Storage |
| RoHS | With Exemptions |
| REACH | SVHC (Pb – CAS 7439-92-1) |
| Lead | Screw Terminals M6 |
| AEC-Q200 | No |
| Typical Component Weight | 3,600 g |
| Miscellaneous | Thermal Resistance = 2.6 C/W. Weight = 15000 grams. |

Dimensions

| | |
|----|---------------|
| D | 136mm +2mm |
| L | 232mm +/-2mm |
| L1 | 235mm +/-2mm |
| S | 50mm +/-0.3mm |
| D1 | 139mm +0.5mm |

Packaging Specifications

| | |
|--------------------|---------------|
| Terminal Type | Bolt - M12x16 |
| Packaging | Bulk, Bag |
| Packaging Quantity | 4 |

Specifications

| | |
|-----------------------|---|
| Capacitance | 2,740 uF |
| Tolerance | 10% |
| Voltage DC | 900 VDC |
| Temperature Range | -40/+85°C |
| Rated Temperature | 75°C |
| Insulation Resistance | 10 MOhms |
| Max dV/dt | 4 V/us |
| ESR | 1 mOhms (1kHz) |
| Ripple Current | 100 Amps (1kHz 40C), 11000 Amps (Peak) |
| Inductance | 80 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.