



Specifications	
Capacitance	4500 uF
Capacitance Tolerance	10%
Voltage DC	900 VDC
Temperature Range	-40/+85°C
Rated Temperature	75°C
Insulation Resistance	10 MOhms
Max dV/dt	4 V/us
ESR	0.95 mOhms (1kHz)
Ripple Current	100 Amps (1kHz 40C), 14000 Amps (Peak)
Inductance	90 nH

Packaging Specifications	
Mounting	Bolt - M12x16
Packaging	Bulk, Bag
Packaging Quantity	2