



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|------------------------------|
| Series | C44U-T |
| Dielectric | Metallized Polypropylene |
| Style | Can |
| Features | DC Filtering, Energy Storage |
| RoHS | With Exemptions |
| Lead | Screw Terminals M6 |
| AEC-Q200 | No |
| Typical Component Weight | 2,000 g |
| Miscellaneous | Thermal Resistance = 4.3C/W. |

Dimensions

| | |
|----|---------------|
| D | 136mm +2mm |
| L | 131mm +/-2mm |
| L1 | 134mm +/-2mm |
| S | 50mm +/-0.3mm |
| D1 | 139mm +0.5mm |

Packaging Specifications

| | |
|--------------------|---------------|
| Terminal Type | Bolt - M12x16 |
| Packaging | Bulk, Bag |
| Packaging Quantity | 4 |

Specifications

| | |
|-----------------------|--------------------------------------|
| Capacitance | 910 uF |
| Tolerance | 10% |
| Voltage DC | 1100 VDC |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Insulation Resistance | 850 MOhms |
| Max dV/dt | 6 V/us |
| ESR | 0.85 mOhms |
| Ripple Current | 60 Amps (1kHz 55C), 5400 Amps (Peak) |
| Inductance | 40 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.