




C4AF, Film, Metallized Polypropylene, Power, 40 uF, 10%, 500 VDC, 250 VAC, 85°C, 52.5 mm



Click her	e for t	the 3D	model.
-----------	---------	--------	--------

General Information	
Series	C4AF
Dielectric	Metallized Polypropylene
Style	Radial
Features	Harsh Environmental Conditions
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	138 g
Miscellaneous	Rth = 10 C/W.

Dimensions	
L	57.5mm +0.8/-0.7mm
Н	50mm +0.3/-0.7mm
Т	35mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	23

Specifications	
Capacitance	40 uF
Tolerance	10%
Voltage DC	500 VDC
Voltage AC	250 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	750 MOhms
Max dV/dt	8 V/us
ESR	40 mOhms
Ripple Current	23.2 Amps Irms (MAX), 320 Amps Ipkr
Inductance	19.5 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO