




C4AF, Film, Metallized Polypropylene, Power, 2 uF, 10%, 630 VDC, 310 VAC, $85^{\circ}\text{C}, 27.5~\text{mm}$



	General Information	
	Series	C4AF
	Dielectric	Metallized Polypropylene
	Style	Radial
	Features	Harsh Environmental Conditions
	RoHS	Yes
	Lead	Wire Leads
	Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
	AEC-Q200	Yes
	Typical Component Weight	19 g
	Miscellaneous	Rth = 33 C/W.

Click here for the 3D model.

Dimensions		
L	31.5mm +0.5/-0.7mm	
Н	28mm +0.2/-0.7mm	
Т	14mm +0.3/-0.7mm	
S	27.5mm +/-0.4mm	
LL	6mm +0/-2mm	
F	0.8mm +/-0.05mm	

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	96

Specifications	
Capacitance	2 uF
Tolerance	10%
Voltage DC	630 VDC
Voltage AC	310 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	15 GOhms
Max dV/dt	40 V/us
ESR	2 mOhms
Ripple Current	5.5 Amps Irms (MAX), 80 Amps Ipkr
Inductance	31.2 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/26/2025 © 2006 - 2025 YAGEO