




AxiMax 400 Comm COG, Ceramic, 0.01 uF, 5%, 100 VDC, COG, AxiMax, Commercial Standard



		Lead
		Failure Rate
Click here for the 3D model.	Click here for the 3D model.	AEC-Q200
		Halogen Free
		<u> </u>
Dimensions		Specifications
D	3.81mm MAX	Capacitance
L	6.6mm MAX	Measurement Condition
LL	25.4mm MIN	Tolerance

0.51mm +0.025/-0.076mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	200

F

General Information			
Series	AxiMax 400 Comm COG		
Description	AxiMax, Commercial Standard		
RoHS	No		
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov / .		
SCIP Number	3465aa18-e916-4945-ab2d-d59 a191a2534		
Termination	Lead (SnPb)		
Lead	Wire Leads		
Failure Rate	N/A		
AEC-Q200	No		
Halogen Free	Yes		

Constitutions	
Specifications	
Capacitance	0.01 uF
Measurement Condition	1 MHz 1.0Vrms
Tolerance	5%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30PPM/C, 1kHz 1.0Vrms
Dissipation Factor	0.1% 1 MHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO