



Click [here](#) for the 3D model.

Dimensions

L	57.5mm +0.8/-0.7mm
H	56mm +0.3/-0.7mm
T	45mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	18

General Information

Series	C4AQ-P
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	193.5 g
Miscellaneous	Rth = 8 C/W.

Specifications

Capacitance	38 uF
Capacitance Tolerance	5%
Voltage DC	1100 VDC
Temperature Range	-55/+125°C
Insulation Resistance	790 MOhms
Max dV/dt	20 V/us
ESR	3.96 mOhms (10kHz 70C)
Ripple Current	29.8 Amps Irms (10kHz 75C), 760 Amps Ipk
Inductance	17 nH