




C4AS, Film, Metallized Polypropylene, Power, 1.2 uF, 10%, 1,200 VDC, 630 VAC, 70°C, 37.5 mm



General Information	
Series	C4AS
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	69.44 g

Click here for the 3D model.

42.5mm -0.7mm
37mm -0.7mm
28mm -0.7mm
37.5mm +/-0.4mm
6mm -2mm
1.2mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	36

Specifications	
Capacitance	1.2 uF
Tolerance	10%
Voltage DC	1200 VDC
Voltage AC	630 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	965 V/us
ESR	4 mOhms (100kHz)
Ripple Current	14 Amps (100kHz 70C), 1158 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/21/2025 © 2006 - 2025 YAGEO