



Click [here](#) for the 3D model.

### Dimensions

D	85mm +/-0.5mm
L	137mm +/-2mm
S	35mm +/-0.5mm

### Packaging Specifications

Terminal Type	Through-Hole
Terminal Type	Bolt - M12x12.5
Packaging	Bulk, Bag
Packaging Quantity	9

### General Information

Series	C44A
Dielectric	Metallized Polypropylene
Style	Can
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	cc1c1ec4-db9e-4815-b26b-e8a34ddfb776
Lead	Threaded Studs M10
AEC-Q200	No
Typical Component Weight	944.4 g
Miscellaneous	Thermal Resistance = 4 C/W.

### Specifications

Capacitance	75 uF
Capacitance Tolerance	5%
Voltage DC	700 VDC
Voltage AC	400 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	30 V/us
ESR	4 mOhms (TYP)
Ripple Current	32 Amps, 2250 Amps (Peak)