



Click [here](#) for the 3D model.

Dimensions

L	32mm +/-0.7mm
H	37mm +/-0.7mm
T	22mm +/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	64

General Information

Series	C4AU
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	39.2 g
Miscellaneous	Rth = 23 C/W.

Specifications

Capacitance	8 uF
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-55/+105°C
Insulation Resistance	3.75 GOhms
Max dV/dt	70 V/us
ESR	6.4 mOhms (10kHz 70C)
Ripple Current	13.4 Amps Irms (10kHz 95C), 560 Amps Ipk
Inductance	28 nH