



Click [here](#) for the 3D model.

Dimensions

D	65mm +/-0.5mm
L	247mm +/-2mm
W	18mm +/-1mm
S	28mm +/-1mm
W1	40mm +/-1mm

Packaging Specifications

Mounting	Bolt - M12x16
Packaging	Bulk, Bag

General Information

Series	C44P-R
Dielectric	Metallized Polypropylene
Style	Can
Features	Single Phase PFC
RoHS	With Exemptions
REACH	SVHC (Pb – CAS 7439-92-1)
SCIP Number	cc1c1ec4-db9e-4815-b26b-e8a34ddfb776
Lead	Threaded Studs M10
AEC-Q200	No
Typical Component Weight	900 g
Miscellaneous	Thermal Resistance = 5.9 C/W.

Specifications

Capacitance	47 uF
Capacitance Tolerance	10%
Voltage AC	640 VAC
Voltage DC	1400 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
Max dV/dt	30 V/us
ESR	1.9029422 mOhms (10kHz)
Ripple Current	49 Amps (10kHz 40C)
Inductance	145 nH