




C44U, Film, Metallized Polypropylene, DC Link, 75 uF, 10%, 1,100 VDC, 31.7 mm



Click here for the 3D model.

76mm +1mm
70mm +0.5mm
76mm +/-1mm
31.7mm +/-0.2mm

Packaging Specifications		
Terminal Type	Bolt - M12x16	
Packaging	Bulk, Bag	
Packaging Quantity	18	

General Information	
Series	C44U
Dielectric	Metallized Polypropylene
Style	Can
Features	Heavy Duty
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	cc1c1ec4-db9e-4815-b26b-e8a3 4ddfb776
Lead	Screw Terminals M6
AEC-Q200	No
Typical Component Weight	8.64 g
Miscellaneous	Thermal Resistance = 8.2 C/W. Weight = 352 grams.

Specifications	
Capacitance	75 uF
Tolerance	10%
Voltage DC	1100 VDC
Temperature Range	-40/+85°C
Rated Temperature	75°C
Insulation Resistance	400 MOhms
Max dV/dt	21 V/us
ESR	1.6 mOhms (10kHz)
Ripple Current	58 Amps (10kHz 40C), 1575 Amps (Peak)
Inductance	40 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO