



Click [here](#) for the 3D model.

General Information

Series	C44U
Dielectric	Metallized Polypropylene
Style	Can
Features	Standard Duty
RoHS	With Exemptions
REACH	SVHC (Pb – CAS 7439-92-1)
Lead	Threaded Studs M8
AEC-Q200	No
Typical Component Weight	740 g
Miscellaneous	Thermal Resistance = 6.4 C/W. Weight = 610 grams.

Dimensions

D	76mm +1mm
L	95mm +0.5mm
L1	101mm +/-1mm
S	31.7mm +/-0.2mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	9

Specifications

Capacitance	120 uF
Tolerance	10%
Voltage DC	1300 VDC
Temperature Range	-40/+85°C
Rated Temperature	75°C
Insulation Resistance	250 MOhms
Max dV/dt	15 V/us
ESR	2.5 mOhms (10kHz)
Ripple Current	43 Amps (10kHz 40C), 1800 Amps (Peak)
Inductance	36 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.