


C4AEJBW5150B3FJ

Not for New Design

C4AE, Film, Metallized Polypropylene, DC Link, 15 uF, 5%, 700 VDC, 85°C, 37.5 mm



Click here for the 3D mode	Click	here	for	the	3D	mode
----------------------------	-------	------	-----	-----	----	------

General Information	
Series	C4AE
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	4 Wire Leads
AEC-Q200	No
Typical Component Weight	39.4 g
Miscellaneous	Thermal Resistance = 20 C/W.

42mm +0.6/-0.7mm
40mm +0.2/-0.7mm
20mm +0.4/-0.7mm
37.5mm +/-0.4mm
10.2mm +/-0.4mm
6mm -2mm
1.2mm +/-0.05mm

Packaging Specifications		
Packaging	Bulk, Box	

Specifications	
Capacitance	15 uF
Tolerance	5%
Voltage DC	700 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	2 GOhms
Max dV/dt	13 V/us
ESR	6.2 mOhms (10kHz 70C)
Ripple Current	10 Amps Irms (10kHz 70C), 196 Amps Ipkr
Inductance	30 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/27/2025 © 2006 - 2025 YAGEO