



Click [here](#) for the 3D model.

Dimensions

L	57.5mm +0.8/-0.7mm
H	65mm +0.3/-0.7mm
T	45mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	18

General Information

Series	C4AQ-P
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	223.8 g
Miscellaneous	Rth = 7 C/W.

Specifications

Capacitance	130 uF
Capacitance Tolerance	5%
Voltage DC	600 VDC
Temperature Range	-55/+125°C
Insulation Resistance	230 MOhms
Max dV/dt	15 V/us
ESR	2.09 mOhms (10kHz 70C)
Ripple Current	42.9 Amps Irms (10kHz 75C), 1950 Amps Ipk
Inductance	19 nH