



Click [here](#) for the 3D model.

### Dimensions

L	42mm +0.6/-0.7mm
H	45mm +0.2/-0.7mm
T	30mm +0.4/-0.7mm
S	37.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	36

### General Information

Series	C4AQ
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Typical Component Weight	68.4 g
Miscellaneous	Rth = 15 C/W.

### Specifications

Capacitance	30 uF
Capacitance Tolerance	5%
Voltage DC	800 VDC
Temperature Range	-55/+105°C
Rated Temperature	70°C
Insulation Resistance	1 GOhms
Max dV/dt	13 V/us
ESR	3.2 mOhms (10kHz 70C)
Ripple Current	23.2 Amps Irms (10kHz 70C), 389 Amps Ipk
Inductance	13 nH