



Click [here](#) for the 3D model.

### Dimensions

|    |                  |
|----|------------------|
| L  | 32mm +0.5/-0.7mm |
| H  | 19mm +0.2/-0.7mm |
| T  | 31mm +0.3/-0.7mm |
| S  | 27.5mm +/-0.4mm  |
| LL | 6mm +0/-2mm      |
| F  | 0.8mm +/-0.05mm  |

### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Box |
| Packaging Quantity | 80        |

### General Information

|                          |                                      |
|--------------------------|--------------------------------------|
| Series                   | C4AQ-M                               |
| Dielectric               | Metallized Polypropylene             |
| Style                    | Radial                               |
| RoHS                     | Yes                                  |
| Lead                     | Wire Leads                           |
| Qualifications           | AEC-Q200, IEC61071, EN61071, VDE0560 |
| AEC-Q200                 | Yes                                  |
| Typical Component Weight | 28.2 g                               |
| Miscellaneous            | Rth = 30 C/W.                        |

### Specifications

|                       |   |
|-----------------------|---|
| Capacitance           | 10 uF                                     |
| Capacitance Tolerance | 5%  |
| Voltage DC            | 700 VDC                                   |
| Temperature Range     | -55/+105°C                                |
| Rated Temperature     | 85°C                                      |
| Insulation Resistance | 3 GOhms                                   |
| Max dV/dt             | 65 V/us                                   |
| ESR                   | 6.4 mOhms (10kHz 70C)                     |
| Ripple Current        | 11.7 Amps Irms (10kHz 70C), 650 Amps Ipkr |
| Inductance            | 16 nH                                     |